

NOTE: The layout may contain optional devices. Please check the final order.

- 1. E5x (13.3)
- 2. SC1T
- 3. UDC5
- 4. LST5/S/1A/-/S1 (1.3)
-electrical cabinet with cooler (option)

- 5. Stacking wagon
- 6. Frame magnets

QUOTATION DRAWING


PI 40/2012

Product
E5x + LST5/S/1A/-/S1 CELL

Customer
STANDARD LAYOUT



Drawing No
L002631
Project No



NOTE: Min. 800 mm of free space behind the machine is necessary for servicing the pneumatics.

Power supply connection point E*

Air connection point P*

Cutting gas connection point C*

Rev	*	*****	*** **/***
-----	---	-------	------------